

Pilot
for Inner devices

	Ref.
2-18 90°	01-510
2-18 60°	01-520
2-18 82°	01-530
2-42 90°	01-550
2-42 60°	01-555
2-42 82°	01-560
2-42 120°	01-570
20-60 90°	01-575
20-60 60°	01-580
40-80 90°	01-590
40-80 60°	01-595
60-100 90°	01-605
80-120 90°	01-620

for Inner Slim Line devices

3-19 90°	03-510
3-19 60°	03-515
10-30 90°	03-520
10-30 60°	03-525
4-42 90°	03-530

for Outer devices

2-18 90°	02-510
2-18 60°	02-515
2-36 90°	02-520
2-36 60°	02-525
10-46 90°	02-535
10-46 60°	02-540
20-60 90°	02-550
20-60 60°	02-555
40-80 90°	02-565
40-80 60°	02-570
60-100 90°	02-580
80-120 90°	02-595

Nut
for Inner and Outer devices

	Ref.
2-18	01-750
2-42	01-760
20-60	01-770
40-80	01-775
60-100	01-780
80-120	01-785

Inner Slim Line

3-19	03-610
10-30	03-615
4-42	03-620

Lock nut
for Inner and Outer devices

2-18	01-755
2-42	01-765
20-60	

Inner Slim Line

3-19	03-611
------	--------

Spring
for Inner and Outer devices

2-18	01-820
2-42	01-825
20-60	01-830
40-80	01-835
60-100	01-837

Inner Slim Line

4-42	03-645
10-30	03-640

Body
for Inner devices

	Ref.
2-18 90° Cyl. Attach.	01-630
2-18 90° CM 1 Attach.	01-635
2-18 60° Cyl. Attach.	01-640
2-18 60° CM 1 Attach.	01-645
2-42 90° CM 1 Attach.	01-650
2-42 90° CM 2 Attach.	01-651
2-42 90° CM 3 Attach.	01-652
2-42 90° Ø 10-16 Attach.	01-655
2-42 90° Ø 12,7 Attach.	01-660
2-42 60° CM 2 Attach.	01-676
2-42 60° CM 3 Attach.	01-677
2-42 60° Ø 12,7 Attach.	01-685
20-60 90° CM 2 Attach.	01-690
20-60 60° CM 2 Attach.	01-695

for Inner Slim Line devices

3-19 90°	
3-19 60° Ø 10 Attach.	03-555
10-30 90°	
10-30 60° CM 2 Attach.	03-561
4-42 90° CM 2 Attach.	03-576

for Outer devices

2-36 90° CM 2 Attach.	02-610
2-36 90° Ø 10-16 Attach.	02-615
10-46 90° CM 2 Attach.	02-630
10-46 90° Ø 10-16 Attach.	02-635
10-46 90° Ø 12,7 Attach.	02-640
20-60 90° CM 2 Attach.	02-645

